

BlendPRO-II

BlendPRO-II adds widescreen blending capability to the ScreenPRO-II family.



Processing includes data doubling to generate overlapped projected regions as well as edge-feathering of the overlapped images. The amount of data overlap and the edge-feather transfer function are user programmable.

The complete widescreen system consists of the BlendPRO-II, up to four ScreenPRO-II seamless switchers, and the ScreenPRO-II controller. The ScreenPRO-II accepts up to eight (8) universal analog inputs and two DVI signals that can be utilized as unscaled background sources or DSK (Down-Stream-Key). ScreenPRO-II HD also accepts HDSI signals for scaling. A MatrixPRO router connected in front of the ScreenPRO-II increases the input source capability of the system to 16.

Applications

BlendPRO-II allows easy transition from presentations involving independent screens to multiple projector wide-screen presentations. Input source selection, seamless switching, and image processing control functions are performed by multiple ScreenPRO-II units. The outputs from the ScreenPRO-IIs are fed to a BlendPRO-II which creates data overlap and edge feathering completely transparent to the operator. Test patterns are provided to support projector alignment.

Technical specifications

Video Input	Input Types: Four (4) Digital DVI channels per DDWG 1.0 on DVI-I connector Resolution: VGA up to UXGA @60 Hz (including all progressive HD resolutions and 1920x1200 and 2048x1080)
Video Output	Four (4) high resolution channels Digital DVI channels per DDWG 1.0 on DVI-I connectors and Analog RGBHV on HD-15 connectors
User Control	Controlled from ScreenPRO-II controller via Ethernet
Physical	2 RU Rackmount Chassis
Input Power	100-240 VAC, 50-60 Hz, 175 W max.
Environmental	Temperature: 0-40 degrees C; Humidity: 0-95% non-condensing