

# Rugged Remote



The rugged Remote (wired) is extremely reliable and shockproof. It was designed by professionals for professionals. It's built to last, even in the most demanding rental & staging applications.

## Technical specifications

<b>Display</b>	4 lines Liquid Cristal Display fully backlit
<b>Keypad</b>	27 keys fully backlit 5 programmable function keys
<b>Connections</b>	2 way hardwired remote XLR port lamp module info port RS 232/422 port switch RS 422T - RS 422NT - RS232
<b>Communication (baud)</b>	XLR fixed at 57600 bps RS 232/RS 422 (9600 bps, 19200 bps, 38400 bps, 57600 bps, 15200 bps)
<b>Communication range</b>	wired up to 300 m (990 ft)
<b>Address</b>	any number between 0 and 255
<b>Power Supply</b>	6x NiCd AA rechargeable batteries (included) or standard batteries 15-30 V DC adaptor 2 charging modes: via external charger or via XLR port of the projector power save mode = automatically switched off after 10 minutes of inactivity
<b>Temperature range</b>	-15 - 70° c (5F - 158F)
<b>Weight</b>	remote control: 1,3 kg (2,8 lbs) receiver: 0,3 kg (0,6 lbs)