

Wireless Rugged Remote



The Wireless Rugged Remote is extremely reliable and shockproof. It was designed by professionals for professionals. It's built to last, even in the most demanding rental & staging applications.

Technical specifications

Display	4 lines Liquid Cristal Display fully backlit
Keypad	27 keys fully backlit 5 programmable function keys
Connections	Radio frequency transceiver 2 way hardwired remote XLR port lamp module info port to facilitate spare lamp management RS 232/422 port switch RS 422T - RS 422NT - RS232
Communication (baud)	XLR fixed at 57600 bps RS 232/RS 422 (9600 bps, 19200 bps, 38400 bps, 57600 bps, 115200 bps)
Communication range	wireless up to 100m (330ft)
Address	any number between 0 and 255
Power Supply	6x NiCd AA rechargeable batteries (included) or standard batteries 15-30 V DC adaptor 2 charging modes: via external charger or via XLR port of the projector power save mode = automatically switched off after 10 minutes of inactivity
Temperature range	-15 - 70° c (5F - 158F)
Weight	remote control: 1,3 kg (2,8 lbs) receiver: 0,3 kg (0,6 lbs)