

# Solaris LC40-M



The LC40 delivers crisp, clear images detailed to perfection. Compatible with a wide variety of signal sources, it is capable of showing analog and digital video as well as data content - scheduled in sequence or picture in picture -, bringing you the ideal medium to display your message to the right audience, at the right time, at the right place.

With optional components that allow you to tailor the display - both in functionality and look & feel - to your specific needs, The LC40 can easily be integrated in any environment. By combining an integrated PC, content management and scheduling software as well as the high-resolution LC40 display, Barco offers you a total solution for dynamic digital signage.

**BARCO**

Visibly yours

# Technische Daten

<b>Technologie</b>	TFT LCD
<b>Panel-Auflösung</b>	1280 x 768 (W-XGA)
<b>Diagonale der aktiven Bildschirmfläche</b>	1010 mm (39.6")
<b>Aktive Bildschirmfläche</b>	862 mm x 517 mm
<b>Hor. Betrachtungswinkel</b>	170°
<b>Vert. Betrachtungswinkel</b>	170°
<b>Lebensdauer</b>	typisch 50.000 h
<b>Gewicht</b>	25 kg
<b>Kontrast</b>	600:1
<b>Helligkeit</b>	450 Nit
<b>Farben</b>	16,8 Millionen
<b>Seitenverhältnis</b>	15:9
<b>Standard-Eingänge</b>	DVI, RGBHV (an BNC), SDI
<b>Bedienung</b>	Bedienung über IP (inklusive internem Hub für LAN-Applikationen) RS232-Steuerung On-Screen-Display (OSD)
<b>Spannungsversorgung</b>	85 V-264 V (50 Hz-60 Hz)
<b>Leistungsaufnahme</b>	270 W (330 W inklusive Kompact-PC)
<b>Betriebstemperatur</b>	5°C bis 40°C
<b>Luftfeuchtigkeit</b>	Max. 85%
<b>Konformität</b>	UL, CE