

ILite 12 MD

12mm, indoor, SMD, 1500 Nit, LED display solution



The most recent addition to Barco's indoor LED product line, the ILite 12 MD LED display is ideally suited to larger indoor installations with relatively high viewing distances. Offering the same high-quality features as the other ILite products, the ILite 12 MD LED display offers a perfect solution to large indoor entertainment or sports venues, where it can be used as center-hung display or end mounted video board.

BARCO

Visibly yours

Technische Daten

Pixel-Pitch	12 mm
Kalibrierte Helligkeit	1500 NIT (calibrated at 6500°K)
LED-Konfiguration	3-in-1 SMD
Pixel-Dichte	6.480/m ² (602/ft ²) 1.296/tile (36x36)
Hor. Betrachtungswinkel	145° + (min. 50% brightness)
Vert. Betrachtungswinkel	145° + (min. 50% brightness)
Kontrast	950:1
Lebensdauer	100.000h (typical use) 45.000h (full white - half brightness)
Leistungsaufnahme	maximum: 400 W/Tile average: 100 W/Tile
Gewicht	13 Kg (28,7 lbs)
Verarbeitung	+12 bit/color (Color) 8 bit/color (Greyscale)
Farben	68,7 billion
Bildwiederholfrequenz	400 Hz (PAL/NTSC minimum)
Temperaturbereich	operating: 0 - 40°C (32 - 104°F) storage: -20 - 60°C (-4 - 140°F)
Luftfeuchtigkeit	operating: 35 - 85% storage: 10 - 90%
Quellen-Kompatibilität	S-Video / Composite / YUV / RGB / SDI / HDSDI / Data DVI up to SXGA
Zertifizierungen	UL - CE - TUV Class A
Abmessungen	Width: 448mm (17.6") Height: 448mm (17.6") Depth: 127mm (5")

Generiert am: Saturday, May 26, 2012
Die angegebenen Informationen und Daten sind typisch für das beschriebene Gerät.
Jede Spezifikation kann sich aber ohne vorherige Ankündigung ändern.
Die aktuelle Version dieser Broschüre finden Sie unter www.barco.com.

BARCO

Visibly yours