

EP10

The Barco EP10 –superb quality,outstanding performance,installation flexibility and ease of operation combined in one cost efficient



Combining superb performance with a compact and elegant appearance,the Barco EP10 digital projector is equally suitable for Alternative Content and Digital Advertizing presentations in the theater and highest quality display in any HD screening room or audio dubbing studio.

Incorporating the latest generation of HDTV (16:9 format)3 chip DLP™technology the advanced EP10 provides images of exceptional brightness, resolution,color depth and contrast. Powerful enough to meet the requirements of Digital Advertizing on up to 10m (32ft)wide Cinema screens in half-light,yet quiet and styl- ish enough to meet the demanding installation needs of the most prestige viewing room,the Barco EP10 also offers a unique degree of flexibility both in installation and control.

BARCO

Visibly yours

Technische Daten

Technologie	3 x 0.8" chip, DLP™
Auflösung	1280 x 720
Kontrast	16 x 9
Helligkeit	3000 ANSI Lumens
Kontrast	1200 : 1
Farben	4.4 m colors
Maximale Bildgröße (diagonal)	10m (32ft)
Abmessungen	282 x 605 x 694 mm (HxWxD)
Gewicht	25 kg
Leistungsaufnahme	1000 W
Geräuschpegel	42 dBA
Eingänge	Native DVI, SDI, Component, S-Video, Composite Optional SDI
Anamorphotische Optik	Not required
Lampe	Size 2 x 250W UHP
Bedienung	RS232 / 422
Spezielle Eigenschaften	16:9 DLP chip format Dual lamp operation

Generiert am: Saturday, May 26, 2012

Die angegebenen Informationen und Daten sind typisch für das beschriebene Gerät.
Jede Spezifikation kann sich aber ohne vorherige Ankündigung ändern.
Die aktuelle Version dieser Broschüre finden Sie unter www.barco.com.

BARCO

Visibly yours