

LD140-8

Barco's LD LED display solution wraps all the desirable LED qualities of brightness, dependability, long lifetime and low maintenance into an affordable



The Barco LD LED display solution has been carefully designed for simplicity and ease of use. Putting LED display technology to work for you has never been easier. Whether you are equipping a retail outlet, museum, or corporate lobby, the Barco LD indoor LED display ensures that you have a straightforward digital signage solution that combines the performance you need at a price you can afford.

BARCO

Visibly yours

Technische Daten

Displaygröße	diagonal: 142" W x H: 3136mm x 1729 mm (124" x 71") surface: 5,6 m ² (60 ft ²)
LED Bauform	3-in-1 SMD
Pixel-Pitch	8 mm
Auflösung	392 x 224
Helligkeit	1200 NIT 1000 NIT (display calibrated at 6500° K)
Hor. Betrachtungswinkel	145° + (min 50% brightness)
Vert. Betrachtungswinkel	145° + (min 50% brightness)
Lebensdauer	100.000h (typ. use) 45.000h (full white - half brightness)
Verarbeitung	+12 bit/color
Farben	68.7 billion
Bildwiederholfrequenz	400 Hz
Leistungsaufnahme	2.240W (Avg) 8.960W (Max)
Temperaturbereich	operating: 0° to 40°C (32° to 140°F) storage: -20° to 60°C (-4° to 140°F)
Gehäuseabmessungen	width: 3372mm (133") height: 2028mm (80") depth: 330mm (13")
Gewicht	620kg - 1367lbs (excl. opt. mounting)
Bildverarbeitungsgerät	D2

Generiert am: Saturday, May 26, 2012
Die angegebenen Informationen und Daten sind typisch für das beschriebene Gerät.
Jede Spezifikation kann sich aber ohne vorherige Ankündigung ändern.
Die aktuelle Version dieser Broschüre finden Sie unter www.barco.com.

BARCO

Visibly yours