


SP-10

Sports Perimeter (SP) solution - optimized for Broadcast



No other company is so well placed to provide a **complete Sports Perimeter Solution** than Barco. The SP-10 consists of cutting-edge visualization hardware and advanced dedicated sports software developed and optimised specifically for broadcast. Having seven years experience in large LED displays in the Sports Market and over twenty years in designing and producing specific visualisation solutions for the broadcast market, Barco is the partner you can rely on to turn your stadium digital.

· Optimised for broadcast · Smart management control software · Easy to install, either fixed or temporary installation · Rugged & reliable · Additional income opportunity

BARCO

Visibly yours

Technische Daten

Kalibrierte Helligkeit	5500 NITS
Pixel-Pitch	20.36 mm (real) 10.18 mm (virtual)
LED-Konfiguration	2R, 1G, 1B
Virtuelle vertikale Auflösung	88 lines
LED-Dichte	9646 LEDs / m ²
Hor. Betrachtungswinkel	120° (50% brightness)
Vert. Betrachtungswinkel	+30° / -25° (50% brightness)
Lebensdauer	100.000h (typical use)
Kontrast	1100:1
Verarbeitung	14 bit
Abmessungen	Width: 1.344 mm / tile Height: 905 mm / tile Depth: 200 mm / tile
Gewicht	84 kg / tile
Leistung	Average: 360W / tile Peak input: 1.450W / tile
Robustheit	IP 65
Temperaturbereich	Operating: -20°C - 40°C (-4° - 104°F) Storage: -20°C - 60°C (-4° - 140°F)
Luftfeuchtigkeit	Operating: 10 - 95% Storage: 10 - 95%
Quellen-Kompatibilität	S-Video, Composite, YUV, RGB, SDI, HDSDI, Data DVI up to UXGA
Zertifizierungen	CE, TUV, FCC Class A, ETL

Generiert am: Saturday, May 26, 2012
Die angegebenen Informationen und Daten sind typisch für das beschriebene Gerät.
Jede Spezifikation kann sich aber ohne vorherige Ankündigung ändern.
Die aktuelle Version dieser Broschüre finden Sie unter www.barco.com.

BARCO

Visibly yours