

iD NR-6

Netzwerkzentrischer 1-Chip-DLP-Projektor mit 6.000 Lumen,
SXGA+



Dieses Produkt ist nur für den chinesischen Markt verfügbar.

Barcos kompakter, für den Einsatz rund um die Uhr ausgelegter Projektor iD NR-6 bietet einen hellen Lichtstrom von 6.000 ANSI-Lumen. Dank seines neuen Farbrads, der BrilliantColor-Verarbeitung, des 2.000:1-Kontrastverhältnisses und seiner Farbkonzanz liefert er eine herausragende Bildqualität. Diese Features werden durch ein verbessertes Design, bei dem die Dauerhaftigkeit im Vordergrund stand, komplettiert.

Multi-windowing with mouse and keyboard

By offering seamless source switching and the inherent possibility to project several sources in fully resizable and editable windows, the iD NR-6 is ideal for interactive meetings. Its network-centricity includes remote maintenance and diagnostics, and also renders it suitable for large-screen videoconferencing. The NR-6 is operated simply with mouse and keyboard, which renders it an excellent tool for small- to medium-sized boardrooms, meeting rooms or other interactive presentation areas.

BARCO

Visibly yours

Technische Daten

| | |
|---------------------------------------|--|
| Lichtstrom | 6,000 ANSI lumens |
| Kontrast | 2,000:1 |
| Auflösung | 1400x1050 SXGA+ |
| Chip-Typ | Single-chip DLP with BrilliantColor processing |
| Lampe | 2x250W UHP |
| Lebensdauer der Lampe | 1,500 hrs per lamp |
| Gewicht | 12,9kg (28,5lbs) / 17,5kg (38,5lbs) shipping weight |
| Abmessungen (BxTxH) | 195mm x 415mm x 590mm / 7"68 x 16"34 x 23"23 |
| Lens Shift Vertikal | -30% to +110% |
| Eingänge | <ul style="list-style-type: none"> • 1x 5-BNC: RGBHV, component video • 1x composite video (BNC) • 1x S-video • 1x VGA (D15 connector) • 1x DVI-D Optional SDI input |
| Kommunikations-Port | 1x RS232 |
| Video | <ul style="list-style-type: none"> • PAL, SECAM, NTSC signals • Composite, S-video, component or RGB formats • All current HDTV standards (720i, 720p, 1080i, 1080p) |
| Daten | <ul style="list-style-type: none"> • DVI sources up to SXGA+ • Apple Macintosh formats • Electronic workstations with a resolution of up to 1600x1200 / 75Hz • All computer graphics formats up to UXGA / 75 Hz |
| Frequenzen | <ul style="list-style-type: none"> • Horizontal 15kHz - 110Hz • Vertical 25Hz - 150Hz |
| Sicherheitsstandards | Compliant with UL1950 and EN1950 |
| Elektromagnetische Interferenz | Compliant with FCC rules and regulations |
| Stromversorgung | 90-254 VAC / 50-60Hz |
| Max. Leistungsaufnahme | 2,400 BTU/h |
| Onboard-Display-Server | <ul style="list-style-type: none"> • Pentium M 1.6GHz processor • 512 MB RAM, 40GB hard disk • Microsoft Windows XP multi-language OS • Barco source and layout selection software • Barco centralized control and maintenance software |

Generiert am: Saturday, May 26, 2012
 Die angegebenen Informationen und Daten sind typisch für das beschriebene Gerät.
 Jede Spezifikation kann sich aber ohne vorherige Ankündigung ändern.
 Die aktuelle Version dieser Broschüre finden Sie unter www.barco.com.

BARCO

Visibly yours