

BarcoGraphics 6300

The BARCOGRAPHICS 6300 offers an unprecedented scope of application possibilities for mobile presenters, speakers and trainers. The unit's attractive, contemporary design is easy to integrate in the most prominent meeting places: boardrooms, training centers, conference rooms, education centers, auditoriums, demo rooms, point-of-sale,...

Why would you buy this projector?

Images really jump off the screen thanks to the high light output, the high native panel resolution and the True Color Reproduction processing.

Place the projector anywhere: in any position or at any distance from the screen. Display whatever source.

Plug 'n Play projection tool thanks to the AutoImage feature, the direct stacking, the motorized zoom, focus and lens shift, ...

Built to last design

Silent running prevents the attention of the audience being distracted from the presented.

BARCO

Visibly yours

Technische Daten

Lichtstrom	2200 ANSI Lumen
LCD-Panels	3 active matrix poly-silicon LCD panels (1.8" diagonal) with a resolution of 1,024 x 768 pixels (aspect ratio 4:3)
Kontrast	>350:1 (full white/full black)
Lampe	400 Watt metal-halide arc lamp with a typical lifetime of 750 hours
Kompatibilität	All current Video sources in Composite, S-VHS, RGB or Component forms All currently proposed HDTV, extended and improved television standards All computer graphics formats from VGA, S-VGA, XGA to S-XGA Most Macintosh computers Electronic workstations with a resolution up to 1280 x 1024 pixels/60 Hz Most sources with a pixel clock up to 135 MHz
Gewicht	Body only: 17.7 kg / 39.0 lbs. Body + lens: 21 - 25 kg / 46.3 - 55.1 lbs.
Bildgröße	For the zoom lenses : 1 - 6 m For the 0.8 lens : 1 - 1.7 m