

BarcoReality 6300

The BARCOREALITY 6300 is a high-resolution yet compact projection system, which delivers dynamic and compelling visual presentations. The performance, versatility and convenient form-factor of this projector makes it a powerful presentation tool for boardrooms, training centers, conference rooms, education centers, auditoriums, CAD/CAM Imaging, design centers,...

Why would you buy this projection unit?

Images really jump off the screen thanks to the high light output, the high native panel resolution and the True Color Reproduction processing.

Place the projector anywhere: in any position or at any distance from the screen. Display whatever source.

Plug 'n Play projection tool thanks to the AutoImage feature, the direct stacking, the motorized zoom, focus and lens shift, ...

Built to last design

Silent running prevents the attention of the audience being distracted from the presented.

BARCO

Visibly yours

Technische Daten

Lichtstrom	2000 ANSI Lumen
LCD-Panels	3 active matrix 1.8" diagonal S-XGA poly-silicon LCD panels (aspect ratio 5:4)
Kontrast	> 350:1 (full white/full black) > 120:1 (5x4 Checkerboard)
Lampe	400 Watt metal-halide arc lamp with a typical lifetime of 750 hours
Kompatibilität	All Current video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in Composite, S-VHS, Component or RGB formats All currently proposed HDTV, extended and improved television standards (Eureka 95, Hi-vision, ACTV, IDTV, EDTV,...) All computer graphics formats from VGA, S-VGA, XGA to S-XGA Most Macintosh computers Electronic Workstations with a resolution up to 2000 x 1280 pixels / 76 Hz Most sources with a pixel clock up to 200 Mhz
Gewicht	Body only: 17.7 kg / 39.0 lbs. Body + lens: 21 - 25 kg / 46.3 - 55.1 lbs.
Bildgröße	From 1-6 m, except for the QGD (0.8:1) lenses