

BarcoGraphics 4000

The BARCOGRAPHICS 4000 entry-level poly-silicon LCD projection system combines high brightness, ease-of-use and outstanding reliability to deliver dynamic visual presentations.

Why would you buy this projection system?

- A compact, lightweight projection unit
- High light output of 2,200 ANSI lumen
- A unique dual-lamp system maximizes the reliability and light efficiency.
- The Digital Gamma Correction circuitry delivers naturally vibrant colors with smooth shading and image gradation.
- The Intelligent Image Resizing feature assures smooth outlines and outstanding picture definition with all types of images.

BARCO

Visibly yours

Technische Daten

Lichtstrom	2,200 ANSI lumen
LCD-Panels	3 active matrix 1.3" poly-silicon LCD panels with Micro Lens Arrays and a resolution of 1024 x 768 pixels (XGA)
Kontrast	>200:1 (full white/full black)
Bildgröße	0.6 - 6 m / 1.8 - 20 ft.
Gewicht	9.2 kg / 20.3 lbs.
Kompatibilität	Compatible with: All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats Digital Video formats: HDTV, 720p and 480p All computer graphics formats from VGA, S-VGA, XGA to S-XGA Electronic workstations with a resolution up to 1280 x 1024 pixels
Lampe	Dual-lamp technology with 160 Watt UHM DC lamps with a typical lifetime of 2,000 hours