

# SLM G5 Performer

A Compact and Smokeproof Projector for Rental & Staging Applications



The Barco SLM G5 provides a compact, multi-purpose solution for any event. Its sleek black chassis is equipped with a 3-chip Digital Light Processing™ (DLP™) subsystem, which features XGA resolution Digital Micro Mirror Devices™ and a state-of-the-art optical system. With its 5000 ANSI lumen light output, the G5 is ideally suited for mid-range applications and an excellent choice for the demanding environments of rental & staging events.

#### **The Performer**

Compact, powerful and able to fulfill a multitude of purposes, Barco's SLM Performer series is the ideal solution for any midrange event.

The versatile SLM G5 has a rugged, sensible design and a light output of 5000 ANSI lumen, making it ideally suited to any application that requires a state-of-the-art projector.

#### **Fast, Easy, Modular ...**

With a modular structure which allows greater accessibility to serviceable parts, interlocking design for direct stacking and hanging and an integrated, no-fuss rigging system, the SLM Performer series offers you an efficient, reliable product on which you can depend - time and time again.

**BARCO**

Visibly yours

# Technische Daten

Lichtstrom	5.000 ANSI lumens
Auflösung	1024 x 786 (native) 1600 x 1200 (max)
DMDTM-Chip	3 high resolution XGA DMD's
Helligkeitsgleichförmigkeit	> 90% for the total screen area
Kontrast	500:1 (full white/full black) 500:1 (full white/full black)
Lampe	Lifetime (max): 1500 Hrs Lifetime (typ): 1000 Hrs Lamp Power: 1,2 kW
Geräuschpegel bei 20°C	< 43
Geräuschpegel bei 35°C	< 50
Netzspannung	110/230 V
Leistungsaufnahme	1.600 W
Umgebungstemperatur	40°C (104F) max
Größe	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
Gewicht (inkl. Rigging-Vorrichtung)	56 kg / 124 lbs
Optiken	BARCO's "click-and-play" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
Lens Shift	Motorized V shift: up to 118 % Motorized H shift: up to 65 %
Gekapseltes optisches System	Yes
Seamless Switching	Standard
ScenergiX	Standard
Feste Eingänge	<ul style="list-style-type: none"> <li>• 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals</li> <li>• 2 Multistandard DVI</li> <li>• SDI input (Serial Digital Input)</li> </ul>
Optionale Eingänge	One free digital input slot for optional input modules: <ul style="list-style-type: none"> <li>• SDI</li> <li>• HD - SDI</li> </ul>
Fernbedienung	<ul style="list-style-type: none"> <li>• RS232 or RS422 loop-through input (D9-connector) for PC based projector control</li> <li>• Communication input (D9-connector) for peripherals</li> <li>• 3 pin male XLR connector for wired remote (standard remote)</li> <li>• 3 pin female XLR connector for bi-directional communication (rugged remote)</li> </ul>

Generiert am: Saturday, May 26, 2012  
Die angegebenen Informationen und Daten sind typisch für das beschriebene Gerät.  
Jede Spezifikation kann sich aber ohne vorherige Ankündigung ändern.  
Die aktuelle Version dieser Broschüre finden Sie unter [www.barco.com](http://www.barco.com).

**BARCO**

Visibly yours