

ILite 6

6mm, indoor, 2000 Nit, LED display solution



The ILite LED display is Barco's answer on the growing market demand for high-resolution indoor LED displays. The Barco ILite 6 offers a 6 mm resolution with an unbeatable light output, color uniformity, contrast, flexibility and last but not least seamless pictures. Due to its high resolution, the LED display module is well suited to form small displays of 1.2 sqm and more without compromising on the resolution

BARCO

Visibly yours

Technische Daten

Helligkeit	2.500 NIT
Kalibrierte Helligkeit	2.000+ NIT
Kontrast	950 : 1 (500 lux) 1.625 : 1 (225 lux)
Visuelle Auflösung	6 mm
Hor. Betrachtungswinkel	> 145°
Vert. Betrachtungswinkel	> 145°
Abmessungen	Width: 0,448 m Height: 0,448 m Depth: 0,1495 m
Gewicht	13 kg
Mittlere Leistungsaufnahme	100 W / tile
Max. Leistungsaufnahme	400 W / tile
Temperaturbereich	operating: 0°C <> 40°C storage: -20°C <> 60°C
Bildgröße	Unlimited
Lebensdauer	45.000h [half brightness]
Verarbeitung	+ 10 bit
Quellen-Kompatibilität	S-Video - Composite - YUV - RGB - SDI - HDSDI - Data DVI up to UXGA

Generiert am: Saturday, May 26, 2012
Die angegebenen Informationen und Daten sind typisch für das beschriebene Gerät.
Jede Spezifikation kann sich aber ohne vorherige Ankündigung ändern.
Die aktuelle Version dieser Broschüre finden Sie unter www.barco.com.

BARCO

Visibly yours