

BarcoGraphics 6400i

The BarcoGraphics 6400i provides a unique solution for high-end visual presentations in boardrooms, conference rooms, training and education centres. High brightness (3,000 ANSI lumens), a new 600 Watt lamp design and state-of-the-art XGA polysilicon LCD panels, which ensures natural, uniform images with a remarkable level of color saturation. Thanks to its optional network capabilities, integration in the company network is easy, reducing the total cost of ownership.

BARCO

Visibly yours

Technische Daten

Lichtstrom	3,000 ANSI lumens
LCD-Panels	3 active matrix 1.8" diagonal XGA polysilicon LCD panels (1024 x 768 in 4:3 aspect ratio)
Kontrast	> 450:1 (full white/full black) > 200:1 (5x4 ANSI checkerboard)
Kompatibilität	All video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in Composite, S-VHS, Component or RGB formats All currently proposed HDTV, extended and improved television standards (1080i, 720p, ...) All computer graphics formats from VGA, S-VGA, XGA to S-XGA Most Macintosh computers Electronic workstations with a resolution up to 1280 x 1024 pixels/76 Hz Most sources with a pixel clock up to 135 MHz
Lampe	600 Watt metal-halide arc lamp Typical lifetime: 1000 hours
Gewicht	Body only: 17.7 kg/39.0 lbs. Body + lens: 21-25 kg/46.3-55.1 lbs.
Bildgröße	From 1-6 m, except for the QGD (0.8:1) lenses