

ILite 3

Ultra high 3mm indoor SMD LED display solution



With its ultra-high 3mm resolution, the ILite 3 is Barco's flagship indoor LED display product. The ILite 3 LED display is renowned for its **absolute picture integrity, robustness and flexible form factor**, giving you the opportunity to use the ILite 3 tiles in any shape (like columns and strips).

Purpose built for the road, Barco's indoor LED tiles form part of a **total rental solution** that includes rugged rental mechanics, sturdy flightcases as well as a powerful, user-friendly processor, which allows you to have your LED display installed and calibrated in no time.

With its **sleek, elegant design**, Barco's ILite 3 LED display is the ultimate LED display solution for applications that deserve a touch of glamour. From a corporate lobby or VIP entertainment area, to a premier Auto or Electronics trade show or a flagship retail store, Barco's ILite 3 LED display brings you the "wow"-effect of large-format display technology combined with the image quality until now reserved for smaller format display technologies.

BARCO

Visibly yours

Technische Daten

| | |
|---------------------------------|--|
| Pixel-Pitch | 3,5 mm |
| Kalibrierte Helligkeit | 1000 NIT |
| LED-Konfiguration | 3-in-1 SMD |
| Hor. Betrachtungswinkel | 145° + (min. 50% brightness) |
| Vert. Betrachtungswinkel | 145° + (min. 50% brightness) |
| Kontrast | 950 : 1 (500 lux) |
| Lebensdauer | 45 000h (50% brightness) |
| Leistungsaufnahme | 120W/tile (max) 45W/tile (average) |
| Gewicht | 4.8 kg (10.6 lbs)/tile 96 kg/m ² (19.6 lbs/ft ²) |
| Verarbeitung | color: 14 bit grey scale: 8 bit |
| Farben | 4,4 trillion |
| Bildwiederholfrequenz | 800 Hz |
| Temperaturbereich | operating: 0 - 40°C (32 - 104°F) storage: -20 - 60°C (-4 - 140°F) |
| Luftfeuchtigkeit | operating: 0 - 85% storage: 0 - 90% |
| Quellen-Kompatibilität | S-Video, Composite, YUV, RGB, SDI, HDSDI, Data DVI up to SXGA |
| Bildgröße | Unlimited |
| Zertifizierungen | UL - CE - TUV - FCC Class A |
| Abmessungen | Width: 258mm (10.16") Height: 193,5mm (7.62") Depth: 98,68mm (3.89") |

Generiert am: Saturday, May 26, 2012
Die angegebenen Informationen und Daten sind typisch für das beschriebene Gerät.
Jede Spezifikation kann sich aber ohne vorherige Ankündigung ändern.
Die aktuelle Version dieser Broschüre finden Sie unter www.barco.com.

BARCO

Visibly yours