

D-Cine Premiere Console Kinoton USA



For more information contact Barco

BARCO

Visibly yours

Technische Daten

Allgemein	Kinoton, SK25DC console.
Beleuchtung	Optional 2kW, 3kW, 5kW, and 7kW Xenon Arc lamp depending on screen size.
Reflektor	Standard f2.0 dichroic glass type.
Stromversorgung	- Lamp power supply - EUR version - IREM 3-7 kW three phase 360-460V 50 Hz - Lamp Power supply - USA version - IREM 3-7kW three phase 187-230V 60 Hz