

# Galaxy NW-12 MK I

3D stereo, network-centric, 12,000 lumens, WUXGA, three-chip DLP projector



Barco's Galaxy NW-12 is an active 3D stereo projector with a native WUXGA (1920x1200) resolution. It's the perfect choice for any single- or multi-projector collaborative display system.

## Maximal ease of use

Thanks to its full compatibility with Barco's XDS Control Center software suite, the Galaxy NW-12 offers direct access to all local and networked sources in a familiar Windows desktop. You can display your sources in multiple windows that can be resized, dragged and made to overlap anywhere on the screen, in any combination of 2D and 3D.

## Supreme stereoscopic quality

With its strong 12,000 lumens light output, Barco's Galaxy NW-12 was designed to operate in bright environments. Its native stereoscopic capabilities, which include both passive and active Infitec, render it a perfect choice for applications that require stereoscopic images of the highest detail.

## Maintenance-free design

The Galaxy NW-12 is designed with one of the lowest noise levels in its class, and a guaranteed long system lifetime due to its fully sealed, liquid-cooled optical engine. This not only prevents dust from entering the projector's interior, it also eliminates routine maintenance procedures and strongly reduces potential system downtime.

## Optimized for system integration

Barco's Galaxy NW-12 is optimized for multi-projector system integration through various features:

- **Edge blending** technology creates one continuous image without blurry overlap zones where projections converge.
- **DynaColor** and **linked constant light output (CLO)** ensure the same light and color

**BARCO**

Visibly yours

# Technical specifications

<b>Light Output</b>	12,000 lumens
<b>Contrast ratio</b>	up to 2,000:1
<b>Resolution</b>	WUXGA (1920x1200px)
<b>Chip Type</b>	Three-chip DLP
<b>Lamp</b>	2 kW xenon lamp
<b>Lamp warranty</b>	750 hrs pro rata warranted
<b>Weight</b>	70kg (154.2lbs)
<b>Dimensions (WxLxH)</b>	590x913x345mm (23.22x35.94x13.58")
<b>Lens Shift</b>	Horizontal up to +/- 65% Vertical up to +/- 110%
<b>Standard inputs</b>	1x 5-BNC (RGBHV, RGBS or RGBsB) 1x composite video (BNC) 1x S-video (4-pin mini DIN) Twin dual-link DVI 3 stereo sync inputs (mini DIN)
<b>Optional Inputs</b>	One free layer (see options)
<b>Communication Port</b>	RS232 (on D9) 10/100 Mb/s Ethernet (on RJ45)
<b>Video</b>	PAL, SECAM, NTSC video signals in Composite, S-video, component or RGB format All current HDTV standards (720i, 720p, 1080i, 1080p) in component or RGB format
<b>Data</b>	All computer graphics formats up to QXGA @ 120 Hz Analog sources with a pixel clock of up to 270 MHz DVI sources with a pixel clock of up to 270 MHz
<b>Safety</b>	ETL60950 and EN60950 CE compliant CCC compliant
<b>AC power</b>	220V-240V
<b>Max Power Consumption</b>	2,800 Watt / 9,560 BTU