

D-Cine DP70

... The Digital Cinema Experience

Incorporating the state-of-the-art Texas Instruments' DLP Cinema™ technology exclusively approved by Hollywood for feature film display the D-Cine Cinema projectors range combines a choice of 35mm lamp consoles with Barco's world leading optical expertise for true Digital Cinema displays of exceptional performance.

Stunning 'Premier' quality film-like images delivered to your cinema without jitter, weave, scratches, flicker or ghosting. Bright, clear and even. First time, every time.

Benefits of the D-Cine DP70 DLP Cinema™ projector

- Based on the Strong DPC 7000 lamp console; no need for modification to the booth or projection ports
- 24P frame per second display for a natural film look
- Meets or exceeds SMPTE screen display standards up to 15 m / 50 ft wide
- Integrated design for simple installation and the most reliable operation
- Dust proof construction to guarantee consistently clean display quality
- Twin anamorphic lens attachment with independent lens alignment
- Liquid cooled Digital Micromirror Devices™
- Provided with local control and LED Status Indication
- Alarm and auto shutdown protection

The first highly integrated range of digital projection and remote control possibilities:

- Optional RC 567 touch screen D-Cine operation and automation control interface for remote control
- Optional Alternative Content Switcher and Router (Acsar) to screen digital movies, any standard of digital advertising plus the wide range of 'alternative content' applications

BARCO

Visibly yours

Spécifications techniques

Commande locale	<ul style="list-style-type: none"> • 4 x LED status indication: OK/ Touch Panel ready/Projector Head ready and Projector Error • 4 x push button control of digital head modes • 4 x user definable lamp house or automation controls • 4 x general purpose relays
Options	<ul style="list-style-type: none"> • Alternative Content Switcher And Router (ACSAR)□ Displays any incoming digital or analog signal, for HDTV movie and alternative digital cinema applications. • Automation Interface□ Compatible with industry standard automation systems • Touch Screen Remote Control□ For full control and diagnostics of the projector, the ACSAR and the automation functions. 19" rack and freestanding / wall mount options.
Contraste	1000:1 (full white/full black)
Résolution	1280x1024 per Red, Green and Blue channels; equivalent to 3.9 million pixels
Luminosité	12fL up to 15 m (50ft.) wide (equivalent to 16fL open gate in a film projector). Brightness uniformity: within 90% over the entire screen area.
Digital MicroMirror Device™ (matrice de micro-miroirs numériques)	3x high resolution S-XGA DLP Cinema™ DMD™
Lentilles primaires	All focal lengths covered by a complete range of Isco Optic and Schneider zoom lenses
Traitement des couleurs	<ul style="list-style-type: none"> Bit depth: 42 bit • Color Shades: 4.4 trillion • Color Gamut: 40% better than HDTV (similar to film)
Poids	Digital head and anamorphic lens holder (without lenses): 33 kg/72.7 lb.
Refroidissement	Integrated 3 chip liquid cooling system and heat exchanger
Éclairage	Optional 2kW, 3kW, 5kW and 7kW Xenon Arc lamp depending on screen size.
Lentilles anamorphiques	Optional Flat and Scope types attached via a twin lens adapter
Entrée vidéo numérique	<p>SMPTE 292M: Serial Digital Interface supporting formats: SMPTE 274M: 1920x1080 in 60 Hz interlaced, 24P or 24 SF SMPTE 260M: 1920x1035 in 60 Hz interlaced SMPTE 296M: 1280x720 in 60 Hz progressive Note: interlaced sources to be encoded with 3:2 Pull-Down DFP Graphics port. Compatible with DVI standard</p>
Réflecteur	Standard f1.5 dichroic metal type
Boîtier	Strong PDC 7000 console
Alimentation	<p>US version Lamp power supply: 3-phase 208 V + N/60 Hz Digital head, cooling pump and touch screen: auto-ranging 80-240 V Lamp console: 110 V</p> <p>EUR Version Lamp power supply: 3-phase 400 V + N/50 Hz Digital head, cooling pump and touch screen: auto-ranging 80-240 V Lamp console: 220 V</p>

Créé le : Sunday, May 27, 2012

Les spécifications techniques sont susceptibles d'être modifiées sans préavis.
 Veuillez consulter les dernières informations disponibles sur www.barco.com.

BARCO

Visibly yours