

CompactLink

Cost-effective solution for data transmission up to 100m in between a digitizer and a LED wall, or in between 2 LED walls.



For certain Rental & Staging applications there is a long distance between the LED display and the digitizer.

Compactlink is a **cost-effective**, optical-based solution for medium range data transmissions **in applications up to 100m**. CompactLink can be used in between the digitizer and the LED wall, but **also in between multiple LED walls**.

Two types of CompactLink are available: 50m or 100 m.

BARCO

Visibly yours

Technical specifications

Order Information	R9853320 CompactLink 50 R9853330 CompactLink 100 R9853340 CompactLink cable interface kit
-------------------	---