

# DP-1500

2K Digital Cinema projector for screens up to 15m (49ft)



Using the 0.98 inch DLP Cinema® Chip from Texas Instruments, Barco presents the DP-1500 – a little powerhouse designed for smaller venues, yet ideal for a host of new markets. For “satellite” theaters at large Cineplex facilities, business conference rooms, specialized “rental” cinema suites and screening rooms at a wide variety of production facilities, the DP-1500 offers Barco quality in an affordable and compact package.

## Key benefits

- Suitable for screens up to 15m wide (screen gain 1.5; 14ft L)
- Compatible with all existing 3D technologies
- Sealed engines protect optical path from dirt & dust
- Advanced DMD cooling extends engine lifetime
- Similar lamp running costs as a 35mm projector

**BARCO**

Visibly yours

# Technical specifications

<b>Digital MicroMirror Device™</b>	3 x 0.98" DC2K dark metal devices
<b>Native resolution</b>	2048 x 1080
<b>Housing</b>	Hermetically sealed DMD™ and optical assembly
<b>Screen Width</b>	Screen width (screen gain 1:5) @ 14ftl * : 15m - 50ft Screen width (screen gain 1:3) @ 14ftl * : 14m - 45ft (* ) = +/- 10 variation possible between units
<b>Mounting</b>	universal pedestal (optional)
<b>Ambient Temperature</b>	max. 35°C / 95°F
<b>Lamp</b>	1.5kW - 3kW Xenon lamp size Lamp power: 1.5kW - 3kW
<b>Contrast ratio</b>	2000:1
<b>Digital Video Inputs</b>	2 x SMPTE 292M inputs 2 x DVI input both selectable as single or as dual link
<b>Prime Lenses</b>	Prime lens (1.2 - 1.8) 0.98" DC2K Prime lens (1.4 - 2.05) 0.98" DC2K Prime lens (1.6 - 2.5) 0.98" DC2K Prime lens (1.95 - 3.2) 0.98" DC2K Prime lens (2.4 - 3.9) 0.98" DC2K
<b>Projector Diagnostics</b>	via PC touch panel via Communicator control software via SNMP agent
<b>Power Requirements</b>	220V 14.000 BTU / hr (with 3kW lamp)
<b>Dimensions</b>	Projector: 505(H) x 689(W) x 1018(D) mm 19.9(H) x 27.1(W) x 40.0(D) inch NB.: min. 5 cm of air inlet spacing required at the bottom of projector
<b>Weight</b>	projector: 90kg (199lbs)
<b>Options</b>	CLO-constant light output ACS-2048 SNMP agent motorized/memorized lens focus, zoom & shift automatic XYZ lamp alignment
<b>Order Information</b>	R9004443