

OL-721

70" full HD DLP LED-lit projection module



Barco's 70" OL-721 LED-lit projection module offers an ergonomically excellent viewing experience, with the sharpest and most saturated colors in full HD resolution (1920x1080).

The OL-721 video wall has been designed for an entirely maintenance-free operation over several years, without any need for consumables. The OL-721 comes with Sense6, a unique sensor technology that provides brightness and color stability over time and across the entire display. Sense6 continuously measures brightness and color and adjusts the color space to provide an image that is most convenient for the human eye. This means that no maintenance or manual adjustments are needed.

Thanks to the small depth of the projection module, the OL-721 video wall can easily be installed in confined spaces. The OL-721's rugged design makes the video wall ideally suited for industrial environments.

BARCO

Visibly yours

Technical specifications

Resolution	Full HD (1920 x 1080px)
Brightness	on-screen: 240 Cd/m ²
On-screen contrast	560,000:1
Display technology	Rear projection DLP
Color	Up to 165% EBU (at maximum color mode)
White point	2,300K 6,500K 9,300K arbitrary
Brightness uniformity	95% ANSI 9
Screen	FXS, with H/V 34°/33° (+/- 3°) half gain angle
Screen gap	Hor: 1.0 mm 0.04", Vert. 0.7 mm 0.03" (@ 25°C)
Color stability	Self calibration with spectrometer based Sense6
Dimensions	<ul style="list-style-type: none"> • Diagonal: 70" • Width: 1,550 mm 61" • Height: 872 mm 34.3" • Depth: 622 mm 24.5" • Weight: Projection Module: < 66 kg 146 lbs • Weight: Pedestal: < 39 kg 86 lbs
Light source	6x redundancy for each of 3 LED's
Light source lifetime	> 60,000h (at 6500k) > 80,000h in eco mode MTBF LED > 500,000 h
Recommended maintenance interval	> 5 years Lifetime warranty against burn-in or image retention
Conditions for operation	10°C-40°C, 50°F-104°F, 80% humidity (nc)
AC input voltage	90 – 240 V, 50-60Hz
Power	170W (eco) 230W (typ.) 350W (max)
Heat dissipation	580 BTU/h (eco) 785 BTU/h (typ.) 1,194 BTU/h (max)
Signal	2x Dual link DVI in / 2x Dual link DVI out
Pixel clock	330 MHz
Input frequency	24 – 62 Hz
Genlock	49 – 61 Hz
Minimum frame delay	1 frame
Signal processing	Loop through Free cropping, free scaling (optional)
Direct ethernet access	Built in web server
Graphical user interface	All settings and operational parameters
Warranty	2 years
Integration to third party equipment	WEB service API (optional)